

Strong. Easy. Robust.

Elbow Fittings WV

Version as plug-in connection for fast and easy connection to the pneumatic energy supplies.

Field of Application

For secure hose connections in automation solutions

Advantages – Your benefit

Suitable for all SCHUNK gripper, rotary, and linear modules, in addition to robot accessories

Flexible utilization for use on pneumatic hoses from various manufacturers

Fittings as plug-in connections for fast hose attachment



Application Example



① Elbow Fitting

② Universal Gripper PGN-plus

③ Universal Rotary Actuator SRU-plus

SCHUNK offers more ...

The following components make the WV even more productive – the perfect complement for highest functionality, flexibility, and process reliability.



Universal Gripper
PGN-plus



Flat Swivel Unit
SRU-plus



Banjo Fittings with One-way
low Control Valves DRV




Adapter Plate

① Further information regarding the products can be found on the following product pages or at www.schunk.com.
Please contact us for further information: SCHUNK technical hotline +49-7133-103-2696

**Technical data**

Description		WV-G1/8-6	WV-G1/8-8	WV-G1/4-6
ID		9937129	9936730	9937170
Thread		G1/8"	G1/8"	G1/4"
Operating pressure	[bar]	-/20	-/20	-/20
min. / max. ambient temperature	[°C]	-10/60	-10/60	-10/60

WV main view



70 Wrench size

Description	G	L1	L2	L3	D1	SW	S4
		[mm]	[mm]	[mm]	[mm]		[mm]
WV-G1/8-6	G1/8"	5	13.5	22	12	13	10
WV-G1/8-8	G1/8"	5	16	25.5	14	13	12
WV-G1/4-6	G1/4"	7	15.5	23.5	12	17	10