

Compact. Easy. Safe.

Banjo Fittings with One-way low Control Valves DRV

Version as plug-in connection for fast and easy connection to the pneumatic energy supplies.

Field of Application

For secure hose connections in automation solutions

Advantages – Your benefit

Suitable for all SCHUNK gripper, rotary, and linear modules, in addition to robot accessories

Flexible utilization for use on pneumatic hoses from various manufacturers

Fittings as plug-in connections for fast hose attachment



Application Example



① Swivel Fitting

② Flow Control Valves

③ Swivel Head SRH-plus

④ 3-Finger Universal Gripper PZN-plus

SCHUNK offers more ...

The following components make the DRV even more productive – the perfect complement for highest functionality, flexibility, and process reliability.



Universal Gripper
PGN-plus



Flat Swivel Unit
SRU-plus



Elbow Fittings WV



Adapter Plate

① Further information regarding the products can be found on the following product pages or at www.schunk.com.
Please contact us for further information: SCHUNK technical hotline +49-7133-103-2696






Technical data

Description		DRV-M3-3	DRV-M5-6	DRV-G8-6	DRV-G4-6	DRV-G8-8
ID		9720005	9936160	9936159	9936161	9936162
Thread		M3	M5	G1/8"	G1/4"	G1/8"
Operating pressure	[bar]	20	20	20	20	20
min. / max. ambient temperature	[°C]	-10/60	-10/60	-10/60	-10/60	-10/60

DRV main view



70 Wrench size

Description	G	L1	L2	L3	D1	SW
DRV-M3-3	M3	2.5	29	11	4.8	
DRV-M5-6	M5	4	21.5	21	10.4	8
DRV-G8-6	G1/8"	5	30	22.5	12	14
DRV-G4-6	G1/4"	6.5	32	24.5	12	17
DRV-G8-8	G1/8"	5	30	23	14	14