

ISO 30

Sonstiges	TRIBOS-Mini SVL		
	Bezeichnung	Idt.-Nr.	Listenpreis
	TRIBOS-Mini SVL-100-12 ø0.5	0215700	185,00 €
	TRIBOS-Mini SVL-100-12 ø1.0	0215701	141,00 €
	TRIBOS-Mini SVL-100-12 ø1.5	0215702	141,00 €
	TRIBOS-Mini SVL-100-12 ø2.0	0215703	141,00 €
	TRIBOS-Mini SVL-100-12 ø2.5	0215704	141,00 €
	TRIBOS-Mini SVL-100-12 ø3.0	0215705	141,00 €
	TRIBOS-Mini SVL-100-12 ø3.5	0215706	141,00 €
	TRIBOS-Mini SVL-100-12 ø4.0	0215707	141,00 €
	TRIBOS-Mini SVL-100-12 ø4.5	0215708	141,00 €

powRgrip zylindrische Aufnahmen/Verlängerungen		
Bezeichnung	Idt.-Nr.	Listenpreis
CYL10/PG10x120	261.071.020	139,00 €
CYL20/PG10x120	262.071.020	133,00 €
CYL20/PG10x160	262.071.040	126,00 €
CYL20/PG10x200	262.071.060	133,00 €
CYL20/PG15x120	262.071.061	126,00 €

Ø0.5-10 L1=62.3	61-16401	175,00 €
Ø0.5-16 L1=63.3	61-25405	184,00 €

Spannzangenfutter ISO30		
Bezeichnung (Ø2.5 bei 30.000 U/min-1)	Idt.-Nr.	Listenpreis
Ø0.5-10 L1=50	61-16375	127,00 €
Ø0.5-13 L1=50	61-20375	127,00 €
Ø0.5-16 L1=60	61-25375	127,00 €
Ø1.5-20 L1=65	61-32375	127,00 €

Spannzangenfutter ISO30 lang		
Bezeichnung (Ø2.5 bei 30.000 U/min-1)	Idt.-Nr.	Listenpreis
Ø0.5-10 L1=80	61-16376	151,00 €

Spannzangenfutter Kegel 11,5/5°		
Bezeichnung	Idt.-Nr.	Listenpreis
Ø0.5-7 L1=24.8	61-12510	243,00 €

Mega Micro Chuck Verlängerungen		
Bezeichnung	Idt.-Nr.	Listenpreis
ST10-MEGA35-120		107,60 l
ST12-MEGA45-130		107,60 l
ST12-MEGA45-160		113,40 l
ST14-MEGA55-160		113,40 l
ST14-MEGA55-200		119,70 l

Superior Clamping and Gripping

