

technical data

RPE 200

product name	unit	RPE 200-...-...-...-
order example		RPE 200-X1000-Y1000-Z100-M
load	[kg]	20
x-axis		
stroke	[mm]	500, 800, 1000, 1200, 1500
acceleration	[m/s ²]	5
speed	[m/s]	1
repeatability	[mm]	+/- 0,08
axis type		B 80-ZSS
drive option		
drive type		BoschRexroth MSK060C
gear type		BoschRexroth GTE120
y-axis		
stroke	[mm]	500, 800, 1000, 1200, 1500
acceleration	[m/s ²]	5
speed	[m/s]	1
repeatability	[mm]	+/- 0,08
axis type		B 140-ZSS
drive option		
drive type		BoschRexroth MSK060C
gear type		BoschRexroth GTE120
z-axis		
stroke	[mm]	100, 300, 500
acceleration	[m/s ²]	2
speed	[m/s]	0,25
repeatability	[mm]	+/- 0,03
axis type		B 80-SSS
drive option		
drive type		BoschRexroth MSK040B
gear type		BoschRexroth GTE120