

Clamping ranges ROTA-S flex with long base jaws

	ROTA-S flex 550	ROTA-S flex 700	ROTA-S flex 1000	ROTA-S flex 1200	ROTA-S flex 1400
	SHF 200	SHF 315	SHF 400	SHF 400	SHF 630
A1 [mm]	95 - 417	222 - 563	168 - 772	315 - 1057	276 - 1097
A2 [mm]	95 - 417	-	-	-	-
A3 [mm]	147 - 469	229 - 570	163 - 766	310 - 1051	281 - 1101
A4 [mm]	174 - 496	339 - 680	285 - 888	432 - 1137	441 - 1262
J1 [mm]	159 - 481	303 - 643	280 - 884	428 - 1169	440 - 1261
J2 [mm]	185 - 507	413 - 753	402 - 1006	550 - 1291	600 - 1422
J3 [mm]	238 - 560	-	-	-	-

[mm]		SZKI 319	SZKI 322	SZKI 409	SZKI 411		
		120 - 556	228 - 656	193 - 797	282 - 887		

[mm]	SZKA 212	SZKA 213	SZKA 216	SZKA 321	SZKA 324	SZKA 409	SZKA 412	SZKA 409	SZKA 412	SZKA 631	SZKA 632
	65 - 387	140 - 462	175 - 497	372 - 557	326 - 666	264 - 765	366 - 867	309 - 1050	411 - 1152	288 - 1101	445 - 1262
Swing diameter	570	570	570	755	765	990	990	1280	1280	1408	1408