


Product overview SCHUNK - ZIMMER



PGN-plus(-P)

GPP

40

5003

50

5004

64

5006

80

5008

100

5010

125

5013

160

5016

200

5025

240

5030

300

5035

380

5045

Gripper type

GPP	PGN-plus / PGN-plus-P
GPD	PZN-plus
GPW	PWG-plus

Series

Stroke / Size

Variant

Zimmer	SCHUNK
N	-1
NC	-1-AS
N0	-1-IS
S	-2
SC	-2-AS
SO	-2-IS


IO-Link

-IL integrated valves and control with IO-Link (only for grippers with IO-Link)

Option

Zimmer	Description	SCHUNK
00	Basic version (IP64 and anti-corrosion)	-SD and -K
10	integrated valves	no standard product
20	up to 130°C	-V
21	IP 67	DPG-plus
24	up to 130°C and IP 67	DPG-plus ...-V
	higher gripping forces	-KVZ (not for PGN-plus-P)
	higher accuracy	-P
	for explosive environments	-EX
AL	cost-optimised variant	JGP

Version (Currently without signification)



Interner Gebrauch – internal use – Interner Gebrauch – internal use – Interner Gebrauch – internal use