


SALES Information

Change of supplier in the product portfolio tool holders

CELSIO heat shrinking chucks and extensions

Differences – please also note the catalogue chapter/PDF CELSIO!



HSK-A 40

CELSIO heat shrinking Ø 3, 4, 5:

- Ø **D6 (new)** - D2 (old) at the top of the chuck
SCHUNK larger



SCHUNK: 12,0 mm (new in the catalog - 1458784 Ø3, 1458785 Ø4, 1458786 Ø5)

SCHUNK: 10,0 mm (Previously in the catalogue - 210107 Ø3, 210108 Ø4, 210109 Ø5)

HSK-A 50

CELSIO heat shrinking Ø 3, 4, 5:


- Ø **D6 (new)** - D2 (old) at the top of the chuck
SCHUNK larger



SCHUNK: 12,0 mm (new in the catalog - 1458793 Ø3, 1458794 Ø4, 1458795 Ø5)

SCHUNK: 10,0 mm (Previously in the catalogue - 210110 Ø3, 210111 Ø4, 210112 Ø5)

CELSIO heat shrinking HSK-A50 **208116 Ø18** und **208117 Ø20** are available again!



HSK-A 63

CELSIO heat shrinking $\varnothing 3, 4, 5$:

- $\varnothing$ **D6 (new)** - D2 (old) at the top of the chuck SCHUNK larger



SCHUNK: 12,0 mm (new in the catalog - **1458801** $\varnothing 3$, **1458802** $\varnothing 4$, **1458803** $\varnothing 5$)

SCHUNK: 10,0 mm (Previously in the catalogue - 210113 $\varnothing 3$, 210114 $\varnothing 4$, 210115 $\varnothing 5$)

CELSIO heat shrinking HSK-A63 L1=130mm **26002761** $\varnothing 3$, **26002762** $\varnothing 4$, **26002763** $\varnothing 5$ und **1454450** $\varnothing 32$ additionally available, have been supplemented!

CELSIO heat shrinking HSK-A63 L1=160mm **26000038** $\varnothing 3$, **26000039** $\varnothing 4$ und **26000040** $\varnothing 5$ additionally available, have been supplemented!

HSK-A 100

No differences



CELSIO heat shrinking HSK-A100 L1=130mm **26002389** $\varnothing 25$ und **1454827** $\varnothing 32$ additionally available, have been supplemented!

HSK-E 40


CELSIO heat shrinking $\varnothing 3, 4, 5$:

- $\varnothing$ **D6 (new)** - D2 (old) at the top of the chuck SCHUNK larger



SCHUNK: 12,0 mm (new in the catalog - **1458806** $\varnothing 3$, **1458807** $\varnothing 4$, **1458808** $\varnothing 5$)

SCHUNK: 10,0 mm (Previously in the catalogue - 210143 $\varnothing 3$, 210144 $\varnothing 4$, 210145 $\varnothing 5$)



HSK-E 50

CELSIO heat shrinking Ø 3, 4, 5:

- Ø **D6 (new)** - D2 (old) at the top of the chuck SCHUNK larger



SCHUNK: 12,0 mm (new in the catalog - **1458810 Ø3, 1458811 Ø4, 1458812 Ø5**)

SCHUNK: 10,0 mm (Previously in the catalogue - 210146 Ø3, 210147 Ø4, 210148 Ø5)

HSK-F 63

CELSIO heat shrinking

- available again!
- version „short“ Ø3 – Ø25
- version L1=130mm Ø6 – Ø25



SK 40

CELSIO heat shrinking Ø 3, 4, 5:


- Ø **D6 (new)** - D2 (old) at the top of the chuck SCHUNK larger



SCHUNK: 12,0 mm (new in the catalog - **1458815 Ø3, 1458816 Ø4, 1458817 Ø5**)

SCHUNK: 10,0 mm (Previously in the catalogue - 210080 Ø3, 210090 Ø4, 210100 Ø5)

CELSIO heat shrinking SK 40 L1=130mm **26000906 Ø3, 26000907 Ø4, 26002788 Ø5 und 26000634 Ø32** additionally available, have been supplemented!



SK 50

No differences



BT 40

CELSIO heat shrinking Ø 3, 4, 5:

- Ø **D6 (new)** - D2 (old) at the top of the chuck SCHUNK larger



SCHUNK: 12,0 mm (new in the catalog - 1458826 Ø3, 1458827 Ø4, 1458828 Ø5)

SCHUNK: 10,0 mm (Previously in the catalogue - 210101 Ø3, 210102 Ø4, 210103 Ø5)

CELSIO heat shrinking BT 40 L1=130mm **1324749** Ø 3, **1324751** Ø 4 und **1324752** Ø5 additionally available, have been supplemented!


BT 50

No differences

CELSIO heat shrinking BT 50 L1=130mm

L1=160mm und L1=200mm additionally available, have been supplemented!





CELSIO SCHUNK CAPTO C4

Ø6-20 additionally available, have been supplemented!

CELSIO SCHUNK CAPTO C5

Ø6-25 additionally available, have been supplemented!



CELSIO SCHUNK CAPTO C6

No differences

CELSIO heat shrinking SCHUNK CAPTO C6 short version (L1=80mm) **26002319** Ø3, **26001855** Ø4 und **26002458** Ø5 additionally available, have been supplemented!

CELSIO heat shrinking SCHUNK CAPTO C6 L1=120mm additionally available, have been supplemented!

CELSIO SCHUNK CAPTO C8 short version Ø6-32 additionally available, have been supplemented!

Additional CELSIO variants have also been added to the portfolio,,

- **DualContact BT30 and BT40**
- **L1=120mm available in different interfaces**
- **Version CoolFlow available in different interfaces, also as extensions**
- **CELSIO with 3° available in different interfaces**
- **HSK-F63 Portfolio available again**

The variants that were previously listed in the catalogue can still be ordered, but with different conditions!