




SCHUNK Spannbacken für ROTA THW3 400–128


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 400	0159103	26	12	32		43	125		54	M12	3
	GBK-V 400	0159158	26	12	32		43	125		54	M12	3
	STN 315-6	0160603	21		32	45	56	110	13	28	M16	4.5


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 315	0155103	12	26	36	62	56	105	15	54	M12	Stahl	3.3


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 400	0162103	32	70	36	136.4	11	Stahl	4.6


Krallenbacken für Außenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Stahl	2.8
	SZKA 321	0139166	12	26	40	53	25	M8	54	M12	Stahl	3.1
	SZKA 324	0139169	12	26	40	53	25	M8	54	M12	Stahl	2.8

Krallenbacken für Innenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKI 319	0166162	12	26	40	53	25	M8	54	M12	Stahl	3.9
	SZKI 322	0166165	12	26	40	53	25	M8	54	M12	Stahl	2.7

Krallenbacken für Stangenspannung


	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKA-ST 311	0182156	12	26	32	50	40	54	M12	Stahl	2.2



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für ROTA THW3 400-128

Pendelbacken

	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	PNK-G 400-2	0190619	99	50	3.7
	PNK-G 400-4	0190621	99	50	4.8
	PNK-G 400-6	0190623	99	50	5.28