




Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 165	0121101	14	30	46	79.7	11	16.6	22	22	M10	Stahl	1.3


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	40 - 76	200	SZA 17-1	0122260	14	30	47	20	M6	20	M10	Stahl	1.2
	62 - 99	200	SZA 17-2	0122261	14	30	47	20	M6	20	M10	Stahl	1
	89 - 126	202	SZA 17-3	0122262	14	30	47	20	M6	20	M10	Stahl	1
	115 - 152	210	SZA 17-4	0122263	14	35	47	20	M6	20	M10	Stahl	1.2



Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	53 - 89	200	SZI 17-1	0123140	14	35	47	20	M6	20	M10	Stahl	1.4
	70 - 106	201	SZI 17-2	0123141	14	40	47	20	M6	20	M10	Stahl	1.5
	92 - 129	212	SZI 17-3	0123142	14	40	47	20	M6	20	M10	Stahl	1.6
	112 - 149	212	SZI 17-4	0123143	14	40	47	20	M6	20	M10	Stahl	1.5

Krallenbacken für Stangenspannung





	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	20 - 56	200	SZA-ST 17-1	0175113	14	30	40	30	20	M10	Stahl	1

Verzahnte Stangen





	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 140	0112165	14	35	60	420	Stahl	6.6
	SBM-STA 140	0112166	14	35	60	420	Aluminium	2.4





Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 165	0120152	14	35	40	80	4	15	20	M10	Stahl	2.1
	SWB 165	0120101	14	35	60	68		15	20	M10	Stahl	2.5
	SWB-FF 160	0120302	14	35	40	72		15	21	M12	Stahl	1.8
	SWB-AL 165	0168105	14	35	60	80		15	20	M10	Aluminium	1.2

Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KMWB-SM 165	0132700	12	120	50	160	50	40	60	25	20	M10	Stahl	4.9
	SWB-SM 165	0169099	14	120	40	160	60	50	59.5	25	20	M10	Stahl	5.6
	KMWB-SA 165	0132800	12	120	40	165	58	48	59.5	25	20	M10	Aluminium	2.2
	SWB-SA 165	0170099	14	120	40	165	58	48	59.5	25	20	M10	Aluminium	1.9

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NKS 1	0143104	14	18.5	6.5		M10	M10 x 25	50
	NKA 1	0145103	14	18.5	6.5	20	M10	M10 x 25	50

