


Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SRK 98	0136111	8	10	20	30	45	3	18	M6	Stahl	0.42
	SRK 112	0136103	8	10	25	30	53	4	18	M8	Stahl	0.67
	SRK 132	0136112	8	10	25	30	60	3	22	M8	Stahl	0.76

