




Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 150	0133114	22	60	86	143	20	27	43	43	M20	Stahl	9



Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	46 - 141	424	SZAJ 38-1	0138135	22	60	85	33	M8	43	M20	Stahl	10.2
	102 - 198	429	SZAJ 38-2	0138136	22	60	85	33	M8	43	M20	Stahl	9
	161 - 258	429	SZAJ 38-3	0138137	22	60	85	33	M8	43	M20	Stahl	7.5
	222 - 320	450	SZAJ 38-4	0138138	22	60	85	33	M8	43	M20	Stahl	7.5
	282 - 380	467	SZAJ 38-5	0138139	22	60	85	33	M8	43	M20	Stahl	8.2
	342 - 400	478	SZAJ 38-6	0138140	22	60	85	33	M8	43	M20	Stahl	9.5

Krallenbacken für Innenspannung



	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	101 - 196	420	SZIJ 38-1	0179132	22	60	85	33	M8	43	M20	Stahl	9.5
	155 - 252	425	SZIJ 38-2	0179133	22	60	85	33	M8	43	M20	Stahl	9.1
	210 - 307	420	SZIJ 38-3	0179134	22	60	85	33	M8	43	M20	Stahl	7.6
	279 - 379	430	SZIJ 38-4	0179135	22	60	85	33	M8	43	M20	Stahl	7.1
	339 - 438	480	SZIJ 38-5	0179136	22	60	85	33	M8	43	M20	Stahl	8.6

Verzahnte Stangen


	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 220	0114550	22	60	120	420	Stahl	23.2
	JBM-STA 220	0114552	22	60	100	420	Aluminium	7



Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KM-WBL 150	0132605	22	60	60	185	10	30	43	M20	Stahl	12.6
	KM-WB 151	0132112	22	60	80	156		36	60	M20	Stahl	14.5
	KM-WB 153	0132132	22	60	80	165		37	43	M20	Stahl	16.1
	KM-WB 155	0132156	22	60	120	165		37	43	M20	Stahl	24.2
	KM-WBAL 150	0132526	22	60	80	145		30	43	M20	Aluminium	5.1

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	S1 [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdreh- moment [Nm]
	NJ 152	0146125	24	22	45.5	16.5	43	M20	M20 x 60	300

