




Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SP-HB 800	0125108	30	75	105	250	22	91.8	60	60	M24	Stahl	29.4
	SP-HB 630	0125106	30	75	88	174.5	30	44.5	50	50	M24	Stahl	16.2

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SP-WB 630	0124107	30	75	90	240	42	65	M24	Stahl	32.9
	SP-WB 800	0124108	30	75	90	300	68	65	M24	Stahl	42

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	NS 240	0140104	30	41	15	M24	M24 x 50	450

