




Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Stahl	0.6

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 160	0153100	8	18	20	40	36		85	25	32	M8	Stahl	1.2
	SFA 160-C1	0154121	8	18	30		55.5	51.5	85	19	32	M8	Stahl	2.7
	SFA 160-C2	0154127	8	18	35		40	36	63	19	32	M8	Stahl	1.6
	SFA 160-C3	0154131	8	18	40		60	56	70	19	32	M8	Stahl	3.3
	SFA 160-C4	0154133	8	18	40		80	76	85	19	32	M8	Stahl	5.6
	SFA-AL 160	0172100	8	18	25	50	46		85	25	32	M8	Aluminium	0.7

