




### Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung   | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|---------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB 400       | 0121107    | 25.5      | 60        | 75        | 140       | 18        | 53        | 31        | 31        | M20       | Stahl     | 8              |
|  | SP-HB 400-500 | 0125105    | 25.5      | 57        | 73        | 160       | 22        | 43.1      | 42        | 42        | M18       | Stahl     | 10.2           |

### Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SP-WB 400   | 0124105    | 25.5      | 60        | 100       | 155       | 35        | 40        | M18       | Stahl     | 18.8           |
|                                                                                   | SP-WB 500   | 0124106    | 25.5      | 60        | 100       | 195       | 37        | 40        | M18       | Stahl     | 24.8           |

