






## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung   | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|---------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB 400       | 0121107    | 25.5      | 60        | 75        | 140       | 18        | 53        | 31        | 31        | M20       | Stahl     | 8              |
|  | SP-HB 400-500 | 0125105    | 25.5      | 57        | 73        | 160       | 22        | 43.1      | 42        | 42        | M18       | Stahl     | 10.2           |


## Verzahnte Stangen

|                                                                                    | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Werkstoff | m/Stück<br>[kg] |
|------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------------|
|   | SBM-ST 250  | 0112190    | 25.5      | 60        | 100       | 420       | Stahl     | 19.2            |
|                                                                                    | SBM-ST 251  | 0112191    | 25.5      | 58        | 160       | 420       | Stahl     | 30.9            |
|  | SBM-STA 250 | 0112187    | 25.5      | 60        | 100       | 420       | Aluminium | 7               |

## Weiche Aufsatzbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SP-WB 500   | 0124106    | 25.5      | 60        | 100       | 195       | 37        | 40        | M18       | Stahl     | 24.8           |

## Nutenstein

|                                                                                     | Bezeichnung | Ident.-Nr. | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Zyl.-Schraube | Max. zul.<br>Anziehdrehmoment<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----|---------------|---------------------------------------|
|  | NS 182      | 0140119    | 25.5      | 67        | 14.5       | M18 | M18 x 90      | 220                                   |