

## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SP-HB 800   | 0125108    | 30        | 75        | 105       | 250       | 22        | 91.8      | 60        | 60        | M24       | Stahl     | 29.4           |
|  | SP-HB 630   | 0125106    | 30        | 75        | 88        | 174.5     | 30        | 44.5      | 50        | 50        | M24       | Stahl     | 16.2           |

## Weiche Aufsatzbacken

|  | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|--|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SP-WB 630   | 0124107    | 30        | 75        | 90        | 240       | 42        | 65        | M24       | Stahl     | 32.9           |

## Nutenstein

|                                                                                   | Bezeichnung | Ident.-Nr. | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Zyl.-Schraube | Max. zul.<br>Anziehdrehmoment<br>[Nm] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----|---------------|---------------------------------------|
|  | NS 240-1    | 0140114    | 30        | 41        | 15         | M24 | M24 x 70      | 450                                   |