





Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	L1 [mm]	b [mm]	Screws	m/set [kg]
	SFGF-K 1200	0814846	30	18	45	51	160	60	60	M16x1.5	6.4
	SFGF-L 1200	0814845	30	18	45	51	535	85	60	M16x1.5	20.7


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	327 - 1172	1280	SZKI 411	0166168	18	30	50	71	33	M8	60	M16	Steel	5.5



Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	309 - 1050	1280	SZKA 409	0139170	18	30	50	71	33	M8	60	M16	Steel	6
	411 - 1152	1280	SZKA 412	0139173	18	30	50	71	33	M8	60	M16	Steel	5.1

Hard Stepped Top Jaws



	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 400	0155104	18	30	45	82	75	130	20	60	M16	Steel	6.8

Soft Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 400	0173104	18	30	330	150	440	85	78	55	160	95	60	M16	Steel	55.6
	SFA-SA 400	0174104	18	30	330	150	440	90	83	60	160	95	60	M16	Aluminum	22.8



Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 400	0153104	18	30	50	80	73		180	50	60	M16	Steel	13.5
	SFA 400-C1	0154116	18	30	60		80	73	130	35	60	M16	Steel	11.8
	SFA 400-C3	0154118	18	30	60		100	93	155	35	60	M16	Steel	21.5
	SFA 400-C4	0154119	18	30	60		120	113	155	35	60	M16	Steel	22.4
	SFA 400-C5	0154120	18	30	80		80	73	130	35	60	M16	Steel	16
	SFA 400-C6	0154125	18	30	58		180	173	160	35	60	M16	Steel	35.1
	SFA 400-C7	0154135	18	30	96		115	108	115	35	60	M16	Steel	25.9
	SFA-AL 400	0172105	18	30	50	80	73		180	50	60	M16	Aluminum	5.1



Technical advice and sales: Tel. +49-7133-103-2750