





Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	GBK 200	0159100	20	10	22		29.5	85		40	M8	1
	GBKL 200	0159120	20	10	22		29.5	105		40	M8	1.2
	GBK-V 200	0159150	20	10	22		29.5	85		40	M8	1
	STNJ 200-5	0160650	14		22	40	47	95	10	25	M12	2.6


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	11 – 85	263	II	SZKA-ST 201	0182152	10	20	22	45	37	40	M8	Steel	0.9


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	53 – 110	263	I	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Steel	1.7
	105 – 180	263	I	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Steel	1.4

Claw jaws for O.D. clamping


	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	26 – 96	264	I	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Steel	1.4
	97 – 172	264	I	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Steel	1.3
	132 – 207	269	I	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Steel	1.2

Hard Stepped Block Jaws


	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 201	0162106	22	54	29	84.8	8	Steel	1.6





Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 200	0155101	10	20	22	42	38	71.7	10	40	M8	Steel	2.4



Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	54 - 87	226	PNK-G 200-2	0190659	76	36	1.2
	87 - 136	262	PNK-G 200-6	0190663	76	36	1.6
	105 - 166	260	PNK-G 200-8	0190665	76	36	1.8

QUENTES fiberglass jaws




	Clamping range ØD	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	55 - 115	TRQK 200-2	0150010	10	20	40	58	72	40	M8	0.76
	20 - 64	TRQK 200-1	0150009	10	20	38	54	91	40	M8	0.74

Soft Full Grip Jaws



	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 200	0173101	10	20	140	64	200	60	56	50	70	27	40	M8	Steel	9
	SFA-SM 201	0173105	10	20	140	64	200	80	76	70	70	27	40	M8	Steel	12.5
	SFA-SA 200	0174101	10	20	140	50	200	58	54	48	72.5	32	40	M8	Aluminum	3.5
	SFA-SA 201	0174105	10	20	140	50	200	80	76	70	72.5	32	40	M8	Aluminum	4.7




Soft Monoblock Jaws

	Description	ID	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB 200	0164100	22		65	40		84	Steel	2.7
	UVB-H 200	0164116	22		85	60		84	Steel	3.2
	UVB-B 200	0164113	22	40	65	38		84	Steel	3.9
	UVB-HS 200	0164119	22		85	60	29	84	Steel	2.67

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 200	0153101	10	20	22	47	43		105	35	40	M8	Steel	2
	SFA 200-C1	0154100	10	20	30		55.5	51.5	100	23	40	M8	Steel	3.2
	SFA 200-C2	0154124	10	20	22		55.5	51.5	100	23	40	M8	Steel	2.2
	SFA 200-C3	0154128	10	20	40		40	36	70	23	40	M8	Steel	2.1
	SFA 200-C4	0154130	10	20	40		60	56	85	23	40	M8	Steel	4
	SFA 200-C5	0154132	10	20	40		80	76	95	23	40	M8	Steel	6.1
	SFA-AL 200	0172102	10	20	25	50	46		105	35	40	M8	Aluminum	0.9

Universal top jaws

	Clamping range ØD	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	m/set [kg]
	135 - 181 - 141 - 187	I	SZKU 200	0139301	10	20	24	48	25	M6	40	M8	0.9
	96 - 143 - 102 - 149	II	SZKU 200	0139301	10	20	24	48	25	M6	40	M8	0.9

