



SCHUNK chuck jaws for ROTA THW3 200-52


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	GBK 160	0159106	18	8	20	27.5	65	32	M8	0.6
	GBK-V 160	0159156	18	8	20	27.5	65	32	M8	0.6


Claw jaws For bar clamping

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SZKA-ST 161	0182150	8	18	22	40	30	32	M8	Steel	0.8


Claw jaws for I.D. clamping

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	SZKI 167	0166150	8	18	35	40	20	M6	32	M8	Steel	0.9
	SZKI 169	0166152	8	18	30	40	20	M6	32	M8	Steel	1.3


Claw jaws for O.D. clamping

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	SZKA 163	0165146	8	18	40	40	20	M6	32	M8	Steel	1
	SZKA 169	0165174	8	18	26	40	20	M6	32	M8	Steel	1
	SZKA 168	0165151	8	18	30	40	20	M6	32	M8	Steel	1.3

Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 140-160 I	0162097	20	43.5	22	58	7	Steel	0.7
	GST 140-160 II	0162098	20	43.5	22	58	7	Steel	0.7

Hard Stepped Top Jaws


	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 160	0155100	8	18	20	36.5	32.5	63	7.5	32	M8	Steel	0.6





Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for ROTA THW3 200-52


QUENTES fiberglass jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	TRQK 160	0150024	8	18	38	54	56	32	M8	0.5



Soft Full Grip Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 160	0173100	8	18	120	40	160	50	46	40	60	23	32	M8	Steel	4.8
	SFA-SA 160	0174100	8	18	120	40	165	50	46	40	59.5	23	32	M8	Aluminum	1.8


Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	UVB 160	0164106	20	55.5	35	65	Steel	1.6

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 160	0153100	8	18	20	40	36		85	25	32	M8	Steel	1.2
	SFA 160-C1	0154121	8	18	30		55.5	51.5	85	19	32	M8	Steel	2.7
	SFA 160-C2	0154127	8	18	35		40	36	63	19	32	M8	Steel	1.6
	SFA 160-C3	0154131	8	18	40		60	56	70	19	32	M8	Steel	3.3
	SFA 160-C4	0154133	8	18	40		80	76	85	19	32	M8	Steel	5.6
	SFA-AL 160	0172100	8	18	25	50	46		85	25	32	M8	Aluminum	0.7

Universal top jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	m/set [kg]
	SZKU 160	0139300	8	18	22	42	20	M6	32	M8	0.7
	SZKU 160	0139300	8	18	22	42	20	M6	32	M8	0.7



Technical advice and sales: Tel. +49-7133-103-2750