

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SRK 250	0136107	16	20	50	80	117	12	40	M16	Steel	8.2
	SRK 315	0136109	16	20	50	80	149	6	50	M16	Steel	10.9

