



3-jaw power chuck with through-hole

## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | T1<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHB-M 800   | 0121160 | 30        | 78        | 87        | 190       | 37        | 52         | 32        | 50        | 50        | M24    | Steel    | 15            |

## Soft Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | M<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SWB-M 800   | 0120452 | 30        | 80        | 110       | 220       | 75        | 45        | 50        | M24    | Steel    | 38.4          |



Technical advice and sales: Tel. +49-7133-103-2750