



## Claw jaws For bar clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description | ID      | N [mm] | B [mm] | H [mm] | T [mm] | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-------------|---------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | 12 - 43           | 185                  | SZA-ST 17-1 | 0175113 | 14     | 30     | 40     | 30     | 20     | M10    | Steel    | 1          |



## Claw jaws for O.D. clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Description | ID      | N [mm] | B [mm] | H [mm] | T [mm] | G  | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-------------|---------|--------|--------|--------|--------|----|--------|--------|----------|------------|
|  | 29 - 63           | 185                  | SZA 17-1    | 0122260 | 14     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.2        |
|                                                                                   | 47 - 86           | 187                  | SZA 17-2    | 0122261 | 14     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1          |
|                                                                                   | 73 - 112          | 188                  | SZA 17-3    | 0122262 | 14     | 30     | 47     | 20     | M6 | 20     | M10    | Steel    | 1          |
|                                                                                   | 99 - 138          | 196                  | SZA 17-4    | 0122263 | 14     | 35     | 47     | 20     | M6 | 20     | M10    | Steel    | 1.2        |



## Hard Stepped Top Jaws

|                                                                                    | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | T [mm] | a [mm] | b [mm] | c [mm] | Screws | Material | m/set [kg] |
|------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|----------|------------|
|  | SHB 165     | 0121101 | 14     | 30     | 46     | 79.7   | 11     | 16.6   | 22     | 22     | M10    | Steel    | 1.3        |

## Serrated bars



|                                                                                     | Description | ID      | N [mm] | B [mm] | H [mm] | L [mm] | Material | m/piece [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|----------|--------------|
|  | SBM-ST 140  | 0112165 | 14     | 35     | 60     | 420    | Steel    | 6.6          |
|  | SBM-STA 140 | 0112166 | 14     | 35     | 60     | 420    | Aluminum | 2.4          |

## Soft Full Grip Jaws



|                                                                                     | Description | ID      | N [mm] | B [mm] | B1 [mm] | Ø D [mm] | H [mm] | H1 [mm] | L [mm] | a [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|---------|----------|--------|---------|--------|--------|--------|--------|----------|------------|
|  | SWB-SM 165  | 0169099 | 14     | 120    | 40      | 160      | 60     | 50      | 59.5   | 25     | 20     | M10    | Steel    | 5.6        |
|  | SWB-SA 165  | 0170099 | 14     | 120    | 40      | 165      | 58     | 48      | 59.5   | 25     | 20     | M10    | Aluminum | 1.9        |



## Soft Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|--------|----------|---------------|
|  | SWBL 165    | 0120152 | 14        | 35        | 40        | 80        | 4          | 15        | 20        | M10    | Steel    | 2.1           |
|                                                                                   | SWB 165     | 0120101 | 14        | 35        | 60        | 68        |            | 15        | 20        | M10    | Steel    | 2.5           |
|                                                                                   | SWB-FF 160  | 0120302 | 14        | 35        | 40        | 72        |            | 15        | 21        | M12    | Steel    | 1.8           |
|  | SWB-AL 165  | 0168105 | 14        | 35        | 60        | 80        |            | 15        | 20        | M10    | Aluminum | 1.2           |

## T-nut

|                                                                                     | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Cyl.-screw | Max. adm.<br>tightening<br>torque<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----|------------|-------------------------------------------|
|   | NKS 1       | 0143104 | 14        | 18.5      | 6.5        |           | M10 | M10 x 25   | 50                                        |
|  | NKA 1       | 0145103 | 14        | 18.5      | 6.5        | 20        | M10 | M10 x 25   | 50                                        |

