

3-jaw power chuck without through-hole

## Soft Top Jaws

|  | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|--|-------------|---------|-----------|-----------|-----------|-----------|-----------|------------|-----------|--------|----------|---------------|
|  | SRK 160     | 0136105 | 10        | 16        | 40        | 60        | 76        | 4          | 25        | M12    | Steel    | 2.9           |



Technical advice and sales: Tel. +49-7133-103-2750