




Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SP-HB 800	0125108	30	75	105	250	22	91.8	60	60	M24	Steel	29.4
	SP-HB 630	0125106	30	75	88	174.5	30	44.5	50	50	M24	Steel	16.2

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SP-WB 630	0124107	30	75	90	240	42	65	M24	Steel	32.9
	SP-WB 800	0124108	30	75	90	300	68	65	M24	Steel	42

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 240-1	0140114	30	41	15	M24	M24 x 70	450

