




## Hard Stepped Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SP-HB 800   | 0125108 | 30        | 75        | 105       | 250       | 22        | 91.8      | 60        | 60        | M24    | Steel    | 29.4          |
|  | SP-HB 630   | 0125106 | 30        | 75        | 88        | 174.5     | 30        | 44.5      | 50        | 50        | M24    | Steel    | 16.2          |

## Soft Top Jaws

|                                                                                   | Description | ID      | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | SP-WB 630   | 0124107 | 30        | 75        | 90        | 240       | 42        | 65        | M24    | Steel    | 32.9          |
|                                                                                   | SP-WB 800   | 0124108 | 30        | 75        | 90        | 300       | 68        | 65        | M24    | Steel    | 42            |

## T-nut

|                                                                                     | Description | ID      | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Cyl.-screw | Max. adm.<br>tightening torque<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----|------------|----------------------------------------|
|  | NS 240-1    | 0140114 | 30        | 41        | 15         | M24 | M24 x 70   | 450                                    |

