



3 weeks leadtime max.

Sonderbacken@de.schunk.com


valid until 31.12.2021

hard claw jaws

chuck size up to [mm]	clamping depth up to [mm]	total height up to [mm]	price 3 pieces set for an order volume of		
			from 3 sets 9 pieces	from 2 sets 3 pieces	from 1 set 3 pieces
			-30%	-20%	0%
up to Ø 390	50	75	700	800	1000
	75	120	770	880	1100
from Ø 400	50	75	840	960	1200
	75	120			

Desired configuration please enter the lathe chuck data as well as desired clamping range, clamping depth or total height		
lathe chuck manufacturer	lathe chuck type	lathe chuck size
Schunk	Rota NCD	255

standard type of claw jaw	desired clamping Ø or range	clamping depth	total height
SZA 25-40	280	35	



- * tooth contour cannot be changed compared to standard type
- * For clamping depth changes > 50%, the threaded hole for support bolts is omitted

inquiry		order		information drawing	
customer No.					
customer name					
contact					
order volume in set		signature			
price per set					