



3 weeks leadtime max.

Sonderbacken@de.schunk.com

Valid until 31.12.2021


Block jaws

Width up to [mm]	Height up to [mm]	Length up to [mm]	Price 3 p. set for order quantity of:			
			from 5 sets 15 pieces	from 3 sets 9 pieces	from 2 sets 6 pieces	from 1 sets 3 pieces
			-40%	-30%	-20%	
30	100	100	504 €	588 €	672 €	840 €
	200	200	546 €	637 €	728 €	910 €
50	150	200	588 €	686 €	784 €	980 €
	250	300	654 €	763 €	872 €	1.090 €
70	100	150	816 €	952 €	1.088 €	1.360 €
	200	250	930 €	1.085 €	1.240 €	1.550 €
	250	300	1.044 €	1.218 €	1.392 €	1.740 €


Desired configuration please enter the changes to the standard type in the fields				
Standard Type	Material	Width B1	Height	Length
	40CrMnMo7 Vergüteter Stahl (no heat treatment)			

Weight-reduced option	
ABSX	
ABST	
GWSX	
GWSW	

ABSX / ABST



GWSX / GWSW



Customer-specific labeling (max. 15 characters)




Inquiry

Order

Customer No.	
Customer Name	
Contact	

1 set consisting of piece	
Ordered quantity in set	
Price per set	

Signature	
-----------	--

Standard Type		W	W1	H	h	L	Interface	Material	W1	H	L
	SMB 630 / 800	65		130	88	230	SFG 630 / 800	40CrMnMo7 tempered not hardened Strength 1080 N/mm²		max. 250	max. 300
	SMB 500	45		130	90	176	SFG 400			max. 225	max. 210
	SMB 400	45		93	53	176	SFG 400				max. 190
	SMB-H 315	32		135	100	140	SFG 315				max. 160
	SMB 315	32		81	46	140	SFG 315			max. 200	max. 130
	SMB-H 250	26		100	70	115	SFG 250				max. 110
	SMB 250	26		70	40	115	SFG 250				
	SMB-H 200	22		80	55	94	SFG 200			max. 125	max. 85
	SMB 200	22		60	35	94	SFG 200				
	SMB-H 160	20		60	39	79	SFG 160				
	SMB 160	20		45	24	79	SFG 160				
 	UVB 630	45		134	87	230	GBK 630	40CrMnMo7 tempered not hardened Strength 1080 N/mm²		max. 250	max. 300
	UVB 500	45		124	77	175	GBK 500			max. 225	max. 210
	UVB 400	32		100	66	148	GBK 400				max. 190
	UVB 315	32		90	52	121	GBK 315				max. 160
	UVB-B 315	32	46	90	52	121	GBK 315		32-70		
	UVB-H 315	32		135	101	121	GBK 315			max. 200	max. 130
	UVB 250	26		84	55	99	GBK 250				
	UVB-B 250	26	46	84	52	99	GBK 315		32-70		
	UVB-H 250	26		115	86	99	GBK 250			max. 150	max. 110
	UVB 200	22		65	40	84	GBK 200				
	UVB-B 200	22	40	65	38	84	GBK 315		32-70		
	UVB-H 200	22		85	60	84	1550			max. 125	max. 85
	UVB 160	20		55,5	35	65	GBK 160				