



SCHUNK chuck jaws for ROTA-M flex 2+2 800

Flexible 4-jaw compensation chuck


Claw jaws

	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Material	m/set [kg]
	SZAU-M 400/4	1457627	25.5	60	75	33	M6	60	Steel	2.5



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SP-HB-M 400-500/4	1457323	25.5	57.5	73	159.1	22	38.3	42	42	M18	Steel	13.6

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Screws	Material	m/piece [kg]
	SBM-M 531/4	1457338	25.5	60	100	195	M20	Steel	35.2

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL-M 400/4	1457325	25.5	60	90	195	6	50	35		Steel	9
	SWB-M 400/4	1457324	25.5	60	90	155		30	35	M20	Steel	21.8



Technical advice and sales: Tel. +49-7133-103-2750