



SCHUNK chuck jaws for ROTA-M flex 2+2 500

Flexible 4-jaw compensation chuck



Claw jaws

	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Material	m/set [kg]
	SZAU 400/4	1457357	25.5	60	75	33	M6	60	Steel	2.2

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 400/4	1457278	25.5	60	75	140	18	53	31	31	M20	Steel	10.8

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB 400/4	1457273	25.5	60	90	155	30	35	M20	Steel	21.6
	SWB-AL 400/4	1457306	25.5	60	100	155	30	35	M20	Aluminum	8.6

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 200	0140103	25.5	29	11	M20	M20 x 40	220



Technical advice and sales: Tel. +49-7133-103-2750