

ADHESO Grip Overview

700 µm Structure

	ID-Number	Product
Soft	1456226	ADHESO G-3-700-W
	1456233	ADHESO G-5-700-W
	1456234	ADHESO G-10-700-W
	1456235	ADHESO G-16-700-W
Medium	1456236	ADHESO G-3-700-M
	1456237	ADHESO G-5-700-M
	1456238	ADHESO G-10-700-M
	1456240	ADHESO G-16-700-M
Hard	1456241	ADHESO G-3-700-H
	1456243	ADHESO G-5-700-H
	1456245	ADHESO G-10-700-H
	1456246	ADHESO G-16-700-H

50 µm Structure

	ID-Number	Product
Soft	1456255	ADHESO G-3-50-W
	1456258	ADHESO G-5-50-W
	1456259	ADHESO G-10-50-W
	1456260	ADHESO G-16-50-W
Medium	1456251	ADHESO G-3-50-M
	1456252	ADHESO G-5-50-M
	1456253	ADHESO G-10-50-M
	1456254	ADHESO G-16-50-M

25 µm Structure

	ID-Number	Product
Soft	1458892	ADHESO G-3-25-W
	1458895	ADHESO G-5-25-W
	1458896	ADHESO G-10-25-W
	1458897	ADHESO G-16-25-W
Medium	1456261	ADHESO G-3-25-M
	1456262	ADHESO G-5-25-M
	1456263	ADHESO G-10-25-M
	1456264	ADHESO G-16-25-M

Please do not use the 25 µm and the 50 µm structure with soft foam
on glas or other similar smooth surfaces!

Workpiece examples

Glas, Painted Metals, Polished Metal, Perspex, Foil

Plastic Injection Molding, Circuit Board, Ceramics, Raw Metals, Painted Packages
--

Fabric (without lint), Carbon, Paper

Inappropriate Conditions

Wet Surfaces Oily Surfaces Coolant
--

G: Grip **W:** Soft (uneven surfaces)
M: Medium (rough surface)
H: Hard (flat surfaces)

Flanges

ID-Number	Product
1449156	ADHESO-K ISO050
1449160	ADHESO-K ISO031.5
1449161	ADHESO-K Meca500
1450896	ADHESO-K IGUS D