




Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	52 - 81	209	HGKHA 170	0122203	12	35	50	20	M6	21	M12	Stahl	1.6
	66 - 95	209	HGKHA 171	0122204	12	35	50	20	M6	21	M12	Stahl	1.3
	88 - 117	209	HGKHA 172	0122205	12	35	50	20	M6	21	M12	Stahl	1.3
	110 - 139	209	HGKHA 173	0122206	12	35	50	20	M6	21	M12	Stahl	1.4
	132 - 161	209	HGKHA 174	0122220	12	35	50	20	M6	21	M12	Stahl	1.3
	154 - 184	229	HGKHA 175	0122221	12	35	50	20	M6	21	M12	Stahl	1.6
	174 - 203	249	HGKHA 176	0122225	12	35	50	20	M6	21	M12	Stahl	1.9

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	D [mm]	Max. zul. Anziehdrehmoment [Nm]
	TS 12	0148107	12	23.2	9	M12		100
	TM 12	0148117		19		M12	17.8	100

