




SCHUNK chuck jaws for KHL 250


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	47 - 100	323	HGKHA 250	0122211	16	45	60	22	M6	29	M16	Steel	4.2
	94 - 121	266	HGKHA 251	0122212	16	45	60	22	M6	29	M16	Steel	2.9
	128 - 155	266	HGKHA 252	0122213	16	45	60	22	M6	29	M16	Steel	2.7
	162 - 190	266	HGKHA 253	0122214	16	45	60	22	M6	29	M16	Steel	2.8
	196 - 224	286	HGKHA 254	0122223	16	45	60	22	M6	29	M16	Steel	2.8


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	FB-SM 250	0120952	16	180	80	250	60	50	79	33	29	M16	Steel	11.9
	FB-SA 250	0120902	16	180	70	250	58	48	87.5	43	29	M16	Aluminum	4.8

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	HB 240	0121154	16	40	60	112	12	33	29	29	M16	Steel	2.8

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 160	0112167	16	50	60	420	Steel	9.7
	SBM-ST 161	0112168	16	40	80	420	Steel	10.2
	SBM-STA 160	0112169	16	40	60	420	Aluminum	2.8



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KHL 250

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FBL 240	0120210	16	40	60	120	4	18	29	M16	Steel	5
	SWB-FB 240	0120202	16	40	60	111		18	29	M16	Steel	4.9
	SWB-FB 241	0120207	16	40	80	111		18	29	M16	Steel	6.5
	FB-AL 250	0120552	16	40	60	111		18	29	M16	Aluminum	1.85

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	D [mm]	Max. adm. tightening torque [Nm]
	TS 16	0148108	16	26.7	12	M16		250
	TM 16	0148118		25		M16	24.5	250



Technical advice and sales: Tel. +49-7133-103-2750