




SCHUNK chuck jaws for KHL 400

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FB 228	0120203	20	50	80	150	31	38	M20	Steel	11

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	D [mm]	Max. adm. tightening torque [Nm]
	TS 20	0148109	20	32.7	16	M20		300
	TM 20	0148119		32		M20	32	300



Technical advice and sales: Tel. +49-7133-103-2750