




SCHUNK chuck jaws for KV3 200


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	50 - 82	211	HGKHA 170	0122203	12	35	50	20	M6	21	M12	Steel	1.6
	63 - 97	211	HGKHA 171	0122204	12	35	50	20	M6	21	M12	Steel	1.3
	85 - 119	211	HGKHA 172	0122205	12	35	50	20	M6	21	M12	Steel	1.3
	107 - 141	211	HGKHA 173	0122206	12	35	50	20	M6	21	M12	Steel	1.4
	129 - 163	211	HGKHA 174	0122220	12	35	50	20	M6	21	M12	Steel	1.3
	151 - 185	231	HGKHA 175	0122221	12	35	50	20	M6	21	M12	Steel	1.6
	171 - 205	251	HGKHA 176	0122225	12	35	50	20	M6	21	M12	Steel	1.9



Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	FB-SM 175	0120951	12	120	50	175	60	50	60	24	21	M12	Steel	6.4
	FB-SA 175	0120901	12	120	40	165	58	48	59.5	24	21	M12	Aluminum	2.2

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	HB 237	0121153	12	30	44	79	8	23	21	21	M12	Steel	1.3

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 120	0112160	12	35	60	420	Steel	6.7
	SBM-ST 121	0112163	12	40	80	420	Steel	10.2
	SBM-STA 120	0112161	12	35	60	420	Aluminum	2.4



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KV3 200

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FBL 237	0120209	12	35	60	95	4	14	21	M12	Steel	3.7
	SWB-FB 235	0120204	12	30	55.5	84		18	21	M12	Steel	2.6
	SWB-FB 237	0120201	12	35	60	90		14	21	M12	Steel	3.7
	FB-AL 175	0120551	12	30	60	84		18	21	M12	Aluminum	1.05

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	D [mm]	Max. adm. tightening torque [Nm]
	TS 12	0148107	12	23.2	9	M12		100
	TM 12	0148117		19		M12	17.8	100



Technical advice and sales: Tel. +49-7133-103-2750