


SCHUNK chuck jaws for 2QLC-LS 200-41


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	26 - 86	227	SZA-ST 16-1	0175100	17	35	40	30	19	M12	Steel	1.2
	14 - 59	223	SZA-ST 20-1	0175101	17	35	45	35	22	M12	Steel	1.5
	17 - 49	237	SZA-ST 25-1	0175102	17	35	45	35	22	M12	Steel	1.8

Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	64 - 124	223	SZI 16-18	0123190	17	35	50	20	M6	19	M12	Steel	1.3
	77 - 136	222	SZI 16-19	0123191	17	40	50	20	M6	19	M12	Steel	1.6
	97 - 156	224	SZI 16-20	0123192	17	40	50	20	M6	19	M12	Steel	1.5
	117 - 177	226	SZI 16-21	0123193	17	40	50	20	M6	19	M12	Steel	1.5
	61 - 108	226	SZI 20-10	0123164	17	35	50	20	M6	22	M12	Steel	1.6
	83 - 137	228	SZI 20-11	0123165	17	40	50	20	M6	22	M12	Steel	2
	114 - 168	227	SZI 20-12	0123166	17	40	50	20	M6	22	M12	Steel	1.7
	61 - 102	242	SZI 25-17	0123180	17	35	55	25	M6	22	M12	Steel	1.9
	79 - 127	227	SZI 25-18	0123181	17	40	55	25	M6	22	M12	Steel	2.2
	136 - 191	241	SZI 25-19	0123182	17	40	55	25	M6	22	M12	Steel	2

Claw jaws for O.D. clamping



	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	46 - 106	223	SZA 16-30	0122110	17	35	50	20	M5	19	M12	Steel	1.3
	65 - 126	226	SZA 16-31	0122111	17	35	50	20	M5	19	M12	Steel	1.2
	88 - 148	226	SZA 16-32	0122112	17	35	50	20	M5	19	M12	Steel	1.1
	106 - 166	227	SZA 16-33	0122113	17	40	50	20	M5	19	M12	Steel	1.2
	128 - 188	249	SZA 16-34	0122114	17	40	50	20	M5	19	M12	Steel	1.6
	31 - 73	226	SZA 20-14	0138195	17	35	50	25	M6	22	M12	Steel	1.8
	48 - 101	226	SZA 20-15	0138196	17	35	50	25	M6	22	M12	Steel	1.5
	76 - 130	227	SZA 20-16	0138197	17	40	50	25	M6	22	M12	Steel	1.5
	103 - 157	228	SZA 20-17	0138198	17	40	50	25	M6	22	M12	Steel	1.6
	188 - 133	251	SZA 20-18	0138199	17	40	50	25	M6	22	M12	Steel	1.8
	35 - 69	241	SZA 25-6	0138176	17	35	55	25	M6	22	M12	Steel	2.3
	56 - 99	226	SZA 25-7	0138177	17	35	55	25	M6	22	M12	Steel	1.7
	103 - 158	230	SZA 25-8	0138178	17	40	55	25	M6	22	M12	Steel	1.8
	138 - 193	260	SZA 25-9	0138179	17	40	55	25	M6	22	M12	Steel	2.4




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for 2QLC-LS 200-41


Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-SM 200	0169101	17	140	64	200	60	50	69.5	35	22	M12	Steel	8.6
	SWB-SM 201	0169106	17	140	64	200	75	65	69.5	35	22	M12	Steel	10.8
	SWB-SA 200	0170101	17	140	50	200	58	48	72.5	35	22	M12	Aluminum	3.4
	SWB-SA 201	0170106	17	140	50	200	75	65	72.5	35	22	M12	Aluminum	4.2

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 200	0121104	17	40	49	72.5	12	18	19	19	M12	Steel	1.6

Jaw blanks


	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a [mm]	Min. distance b [mm]	Screws	Material	m/piece [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Steel	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Steel	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Steel	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Steel	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Steel	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Steel	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Steel	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Steel	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Steel	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Steel	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Steel	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Steel	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Steel	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Steel	3.3




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for 2QLC-LS 200-41




Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	59 - 86	217	PNS-Z 200-1	0190138	56	30	1.2
	60 - 89	219	PNS-Z 200-2	0190139	56	30	1.3
	89 - 118	241	PNS-Z 200-3	0190140	56	30	1.4
	119 - 148	239	PNS-Z 200-4	0190141	56	30	1.5
	45 - 70	233	PNS-Z 250-17-1	0190100	56	35	1.6
	103 - 122	246	PNS-Z 250-17-4	0190103	56	35	2.2
	109 - 131	246	PNS-Z 250-17-5	0190104	56	35	2.4

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 170	0112170	17	40	60	420	Steel	7.6
	SBM-ST 171	0112171	17	40	80	420	Steel	10.2
	SBM-ST 172	0112172	17	40	100	420	Steel	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminum	2.8

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL 200	0120153	17	35	40	98	4	15	22	M12	Steel	2.6
	CWB 200	0100006	17	40	40	90		25	22	M12	Steel	2.7
	SWB 200	0120104	17	40	60	90		25	22	M12	Steel	4.1
	SWB-AL 200	0168101	17	40	60	90		25	22	M12	Aluminum	1.5



Technical advice and sales: Tel. +49-7133-103-2750