


SCHUNK Spannbacken für 3QLC/K 200

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	66 - 88	220	PNS-M 200-14-1	0160232	55	30	1.3
	96 - 121	244	PNS-M 200-14-2	0160233	55	30	1.5
	126 - 151	243	PNS-M 200-14-3	0160234	55	30	1.6



Technische Beratung und Verkauf: Tel. +49-7133-103-2750