


SCHUNK Spannbacken für 3QLC/K 315

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	76 - 111	291	PNS-M 315-21-1	0160223	68	35	2.35
	97 - 165	336	PNS-M 315-21-2	0160224	68	35	2.45
	153 - 211	334	PNS-M 315-21-3	0160225	68	35	2.6
	163 - 238	355	PNS-M 315-21-4	0160226	68	35	2.9



Technische Beratung und Verkauf: Tel. +49-7133-103-2750