


SCHUNK Spannbacken für 3QLC/K 400

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	134 - 167	338	PNS-Z 315-2	0190111	64	35	2.3
	207 - 261	381	PNS-Z 315-4	0190113	64	35	2.7
	207 - 299	426	PNS-Z 315-5	0190114	64	35	3.2



Technische Beratung und Verkauf: Tel. +49-7133-103-2750