



# SCHUNK Spannbacken für 3QLC-LS 160-30


## Backenrohlinge

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Min. Abstand<br>a (Backen-<br>spitze bis<br>erste<br>Bohrung)<br>[mm] | Min. Abstand<br>b (Erste bis<br>zweite<br>Bohrung)<br>[mm] | Schrauben | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------------------------------------------------------------------|------------------------------------------------------------|-----------|-----------|-----------------|
|  | SBM 31      | 0112100    | 17        | 40        | 40        | 70        | 12                                                                    | 22                                                         | M12       | Stahl     | 0.9             |
|                                                                                   | SBM 32      | 0112101    | 17        | 40        | 40        | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 1.1             |
|                                                                                   | SBM 33      | 0112102    | 17        | 40        | 40        | 105       | 12                                                                    | 22                                                         | M12       | Stahl     | 1.2             |
|                                                                                   | SBM 34      | 0112103    | 17        | 40        | 60        | 70        | 12                                                                    | 22                                                         | M12       | Stahl     | 1.3             |
|                                                                                   | SBM 35      | 0112104    | 17        | 40        | 60        | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 1.7             |
|                                                                                   | SBM 36      | 0112105    | 17        | 40        | 60        | 105       | 12                                                                    | 22                                                         | M12       | Stahl     | 2               |
|                                                                                   | SBM 361     | 0112136    | 17        | 40        | 60        | 120       | 12                                                                    | 22                                                         | M12       | Stahl     | 2.2             |
|                                                                                   | SBM 3610    | 0112107    | 17        | 40        | 100       | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 2.7             |
|                                                                                   | SBM 3612    | 0112108    | 17        | 40        | 120       | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 3.4             |
|                                                                                   | SBM 3615    | 0112139    | 17        | 50        | 80        | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 2.7             |
|                                                                                   | SBM 368     | 0112106    | 17        | 40        | 80        | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 2.3             |
|                                                                                   | SBM 37      | 0112109    | 17        | 60        | 60        | 70        | 12                                                                    | 22                                                         | M12       | Stahl     | 1.9             |
|                                                                                   | SBM 38      | 0112110    | 17        | 60        | 60        | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 2.4             |
|                                                                                   | SBM 40      | 0112111    | 17        | 80        | 60        | 90        | 12                                                                    | 22                                                         | M12       | Stahl     | 3.3             |

## Harte Stufenaufsatzbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB 175     | 0121103    | 17        | 35        | 44        | 64.7      | 10        | 28        | 19        |           | M12       | Stahl     | 1.2            |
|                                                                                     | SHB 200     | 0121104    | 17        | 40        | 49        | 72.5      | 12        | 18        | 19        | 19        | M12       | Stahl     | 1.6            |

## Krallenbacken für Außenspannung


|                                                                                     | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 34 - 60            | 176                   | SZA 16-30   | 0122110    | 17        | 35        | 50        | 20        | M5 | 19        | M12       | Stahl     | 1.3            |
|                                                                                     | 53 - 79            | 179                   | SZA 16-31   | 0122111    | 17        | 35        | 50        | 20        | M5 | 19        | M12       | Stahl     | 1.2            |
|                                                                                     | 76 - 101           | 179                   | SZA 16-32   | 0122112    | 17        | 35        | 50        | 20        | M5 | 19        | M12       | Stahl     | 1.1            |
|                                                                                     | 93 - 120           | 180                   | SZA 16-33   | 0122113    | 17        | 40        | 50        | 20        | M5 | 19        | M12       | Stahl     | 1.2            |
|                                                                                     | 115 - 142          | 202                   | SZA 16-34   | 0122114    | 17        | 40        | 50        | 20        | M5 | 19        | M12       | Stahl     | 1.6            |
|                                                                                     | 40 - 55            | 179                   | SZA 20-15   | 0138196    | 17        | 35        | 50        | 25        | M6 | 22        | M12       | Stahl     | 1.5            |
|                                                                                     | 64 - 84            | 181                   | SZA 20-16   | 0138197    | 17        | 40        | 50        | 25        | M6 | 22        | M12       | Stahl     | 1.5            |
|                                                                                     | 92 - 111           | 182                   | SZA 20-17   | 0138198    | 17        | 40        | 50        | 25        | M6 | 22        | M12       | Stahl     | 1.6            |
|                                                                                     | 120 - 141          | 205                   | SZA 20-18   | 0138199    | 17        | 40        | 50        | 25        | M6 | 22        | M12       | Stahl     | 1.8            |
|                                                                                     | 91 - 111           | 183                   | SZA 25-8    | 0138178    | 17        | 40        | 55        | 25        | M6 | 22        | M12       | Stahl     | 1.8            |
|                                                                                     | 128 - 146          | 213                   | SZA 25-9    | 0138179    | 17        | 40        | 55        | 25        | M6 | 22        | M12       | Stahl     | 2.4            |




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für 3QLC-LS 160-30



## Krallenbacken für Innenspannung

|                                                                                   | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 52 - 78            | 177                   | SZI 16-18   | 0123190    | 17        | 35        | 50        | 20        | M6 | 19        | M12       | Stahl     | 1.3            |
|                                                                                   | 66 - 90            | 176                   | SZI 16-19   | 0123191    | 17        | 40        | 50        | 20        | M6 | 19        | M12       | Stahl     | 1.6            |
|                                                                                   | 85 - 110           | 178                   | SZI 16-20   | 0123192    | 17        | 40        | 50        | 20        | M6 | 19        | M12       | Stahl     | 1.5            |
|                                                                                   | 105 - 131          | 180                   | SZI 16-21   | 0123193    | 17        | 40        | 50        | 20        | M6 | 19        | M12       | Stahl     | 1.5            |
|                                                                                   | 79 - 91            | 181                   | SZI 20-11   | 0123165    | 17        | 40        | 50        | 20        | M6 | 22        | M12       | Stahl     | 2              |
|                                                                                   | 102 - 122          | 180                   | SZI 20-12   | 0123166    | 17        | 40        | 50        | 20        | M6 | 22        | M12       | Stahl     | 1.7            |
|                                                                                   | 124 - 144          | 194                   | SZI 25-19   | 0123182    | 17        | 40        | 55        | 25        | M6 | 22        | M12       | Stahl     | 2              |


## Krallenbacken für Stangenspannung

|                                                                                   | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | 14 - 39            | 180                   | SZA-ST 16-1 | 0175100    | 17        | 35        | 40        | 30        | 19        | M12       | Stahl     | 1.2            |

## Segmentbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|   | SWB-SM 160  | 0169100    | 17        | 120       | 40         | 160         | 60        | 50         | 59.5      | 25        | 22        | M12       | Stahl     | 5.7            |
|  | SWB-SA 160  | 0170100    | 17        | 120       | 40         | 165         | 58        | 48         | 59.5      | 22        | 22        | M12       | Aluminium | 2.2            |

## Verzahnte Stangen





|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Werkstoff | m/Stück<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | SBM-ST 170  | 0112170    | 17        | 40        | 60        | 420       | Stahl     | 7.6             |
|                                                                                     | SBM-ST 171  | 0112171    | 17        | 40        | 80        | 420       | Stahl     | 10.2            |
|                                                                                     | SBM-ST 172  | 0112172    | 17        | 40        | 100       | 420       | Stahl     | 12.8            |
|  | SBM-STA 170 | 0112173    | 17        | 40        | 60        | 420       | Aluminium | 2.8             |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für 3QLC-LS 160-30

## Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|----------------|
|  | SWBL 160    | 0120151    | 17        | 35        | 40        | 78        | 4          | 15        | 22        | M12       | Stahl     | 1.9            |
|  | CWB 160     | 0100005    | 17        | 35        | 40        | 70        |            | 15        | 22        | M12       | Stahl     | 1.7            |
|  | SWB 160     | 0120102    | 17        | 40        | 60        | 70        |            | 15        | 22        | M12       | Stahl     | 3.1            |
|  | SWB-AL 160  | 0168100    | 17        | 40        | 60        | 70        |            | 15        | 22        | M12       | Aluminium | 1.2            |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750