



SCHUNK chuck jaws for 3QLC-LS 160-30


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	14 - 39	180	SZA-ST 16-1	0175100	17	35	40	30	19	M12	Steel	1.2



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	52 - 78	177	SZI 16-18	0123190	17	35	50	20	M6	19	M12	Steel	1.3
	66 - 90	176	SZI 16-19	0123191	17	40	50	20	M6	19	M12	Steel	1.6
	85 - 110	178	SZI 16-20	0123192	17	40	50	20	M6	19	M12	Steel	1.5
	105 - 131	180	SZI 16-21	0123193	17	40	50	20	M6	19	M12	Steel	1.5
	79 - 91	181	SZI 20-11	0123165	17	40	50	20	M6	22	M12	Steel	2
	102 - 122	180	SZI 20-12	0123166	17	40	50	20	M6	22	M12	Steel	1.7
	124 - 144	194	SZI 25-19	0123182	17	40	55	25	M6	22	M12	Steel	2

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	34 - 60	176	SZA 16-30	0122110	17	35	50	20	M5	19	M12	Steel	1.3
	53 - 79	179	SZA 16-31	0122111	17	35	50	20	M5	19	M12	Steel	1.2
	76 - 101	179	SZA 16-32	0122112	17	35	50	20	M5	19	M12	Steel	1.1
	93 - 120	180	SZA 16-33	0122113	17	40	50	20	M5	19	M12	Steel	1.2
	115 - 142	202	SZA 16-34	0122114	17	40	50	20	M5	19	M12	Steel	1.6
	40 - 55	179	SZA 20-15	0138196	17	35	50	25	M6	22	M12	Steel	1.5
	64 - 84	181	SZA 20-16	0138197	17	40	50	25	M6	22	M12	Steel	1.5
	92 - 111	182	SZA 20-17	0138198	17	40	50	25	M6	22	M12	Steel	1.6
	120 - 141	205	SZA 20-18	0138199	17	40	50	25	M6	22	M12	Steel	1.8
	91 - 111	183	SZA 25-8	0138178	17	40	55	25	M6	22	M12	Steel	1.8
	128 - 146	213	SZA 25-9	0138179	17	40	55	25	M6	22	M12	Steel	2.4

Full Grip Jaws


	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-SM 160	0169100	17	120	40	160	60	50	59.5	25	22	M12	Steel	5.7
	SWB-SA 160	0170100	17	120	40	165	58	48	59.5	22	22	M12	Aluminum	2.2




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for 3QLC-LS 160-30



Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 175	0121103	17	35	44	64.7	10	28	19		M12	Steel	1.2
	SHB 200	0121104	17	40	49	72.5	12	18	19	19	M12	Steel	1.6

Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Min. distance a [mm]	Min. distance b [mm]	Screws	Material	m/piece [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Steel	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Steel	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Steel	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Steel	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Steel	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Steel	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Steel	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Steel	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Steel	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Steel	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Steel	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Steel	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Steel	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Steel	3.3

Serrated bars





	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 170	0112170	17	40	60	420	Steel	7.6
	SBM-ST 171	0112171	17	40	80	420	Steel	10.2
	SBM-ST 172	0112172	17	40	100	420	Steel	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminum	2.8



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for 3QLC-LS 160-30

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL 160	0120151	17	35	40	78	4	15	22	M12	Steel	1.9
	CWB 160	0100005	17	35	40	70		15	22	M12	Steel	1.7
	SWB 160	0120102	17	40	60	70		15	22	M12	Steel	3.1
	SWB-AL 160	0168100	17	40	60	70		15	22	M12	Aluminum	1.2



Technical advice and sales: Tel. +49-7133-103-2750