


SCHUNK chuck jaws for 3QLC/K 400

Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	134 - 167	338	PNS-M 315-21-2	0160224	68	35	2.45
	207 - 261	381	PNS-M 315-21-4	0160226	68	35	2.9



Technical advice and sales: Tel. +49-7133-103-2750