



SCHUNK Spannbacken für 3QLC-KT 400


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	68 - 236	409	SZA 25-37	0138180	21	50	58	25	M8	28	M16	Stahl	3.3
	108 - 276	409	SZA 25-38	0138181	21	50	58	25	M8	28	M16	Stahl	2.9
	157 - 326	412	SZA 25-39	0138182	21	50	58	25	M8	28	M16	Stahl	2.7
	204 - 374	448	SZA 25-40	0138183	21	50	58	25	M8	28	M16	Stahl	3.2
	46 - 214	419	SZA 31-10	0138184	21	50	58	25	M8	28	M16	Stahl	3.4
	103 - 271	420	SZA 31-11	0138185	21	50	58	25	M8	28	M16	Stahl	3.4
	168 - 337	419	SZA 31-12	0138186	21	50	58	25	M8	28	M16	Stahl	3.2
	232 - 402	478	SZA 31-13	0138187	21	50	58	25	M8	28	M16	Stahl	4.5


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	97 - 264	416	SZI 25-34	0123183	21	50	58	25	M8	28	M16	Stahl	3.5
	138 - 306	419	SZI 25-35	0123184	21	50	58	25	M8	28	M16	Stahl	3.2
	183 - 351	418	SZI 25-36	0123185	21	50	58	25	M8	28	M16	Stahl	3
	80 - 234	425	SZI 31-11	0123186	21	50	58	25	M8	28	M16	Stahl	4.1
	127 - 289	418	SZI 31-12	0123187	21	50	58	25	M8	28	M16	Stahl	4.2
	194 - 363	417	SZI 31-13	0123188	21	50	58	25	M8	28	M16	Stahl	3.9

Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	37 - 207	411	SZA-ST 25-2	0175103	21	45	50	40	28	M16	Stahl	2.7
	20 - 175	418	SZA-ST 31-1	0175104	21	45	50	40	28	M16	Stahl	3.3

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	96 - 113	275	PNS-Z 250-21-2	0190106	64	35	2
	100 - 135	294	PNS-Z 250-21-3	0190107	64	35	2.1
	152 - 179	303	PNS-Z 250-21-4	0190108	64	35	2.3
	161 - 198	315	PNS-Z 250-21-5	0190109	64	35	2.3
	80 - 109	288	PNS-Z 315-1	0190110	64	35	2
	94 - 166	337	PNS-Z 315-2	0190111	64	35	2.3
	157 - 208	331	PNS-Z 315-3	0190112	64	35	2.5
	167 - 260	380	PNS-Z 315-4	0190113	64	35	2.7
	201 - 298	425	PNS-Z 315-5	0190114	64	35	3.2