



SCHUNK chuck jaws for F+ 630


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	SFG 630	0157106	40	24	65	58	230	82	M20	17.1



Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	232 - 497	801	I	SZKA 631	0139200	24	40	65	97	42	M8	82	M20	Steel	13
	392 - 658	801	I	SZKA 632	0139201	24	40	65	97	42	M8	82	M20	Steel	11.8
	85 - 324	799	II	SZKA 631	0139200	24	40	65	97	42	M8	82	M20	Steel	13
	209 - 485	799	II	SZKA 632	0139201	24	40	65	97	42	M8	82	M20	Steel	11.8

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 630	0155106	24	40	65	105	97	185	30	82	M20	Steel	18

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 630	0153106	24	40	65	118	110	260	70	82	M20	Steel	39.6
	SFA-AL 630	0172106	24	40	65	118	110	260	70	82	M20	Aluminum	14.8



Technical advice and sales: Tel. +49-7133-103-2750