



SCHUNK chuck jaws for KGH/KGHF 175



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	14 - 44	183	SZA-ST 16-1	0175100	17	35	40	30	19	M12	Steel	1.2


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	28 - 65	180	SZA 16-30	0122110	17	35	50	20	M5	19	M12	Steel	1.3
	47 - 84	180	SZA 16-31	0122111	17	35	50	20	M5	19	M12	Steel	1.2
	69 - 106	180	SZA 16-32	0122112	17	35	50	20	M5	19	M12	Steel	1.1
	87 - 125	185	SZA 16-33	0122113	17	40	50	20	M5	19	M12	Steel	1.2
	109 - 147	205	SZA 16-34	0122114	17	40	50	20	M5	19	M12	Steel	1.6

Full Grip Jaws

	Description	ID	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-SM 160	0169100	17	120	40	160	60	50	59.5	25	22	M12	Steel	5.7
	SWB-SA 160	0170100	17	120	40	165	58	48	59.5	22	22	M12	Aluminum	2.2

Hard Stepped Top Jaws


	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB 175	0121103	17	35	44	64.7	10	28	19		M12	Steel	1.2
	SHB 200	0121104	17	40	49	72.5	12	18	19	19	M12	Steel	1.6




Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KGH/KGHF 175


Jaw blanks

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/piece [kg]
	SBM 31	0112100	17	40	40	70	12	22	M12	Steel	0.9
	SBM 32	0112101	17	40	40	90	12	22	M12	Steel	1.1
	SBM 33	0112102	17	40	40	105	12	22	M12	Steel	1.2
	SBM 34	0112103	17	40	60	70	12	22	M12	Steel	1.3
	SBM 35	0112104	17	40	60	90	12	22	M12	Steel	1.7
	SBM 36	0112105	17	40	60	105	12	22	M12	Steel	2
	SBM 361	0112136	17	40	60	120	12	22	M12	Steel	2.2
	SBM 3610	0112107	17	40	100	90	12	22	M12	Steel	2.7
	SBM 3612	0112108	17	40	120	90	12	22	M12	Steel	3.4
	SBM 3615	0112139	17	50	80	90	12	22	M12	Steel	2.7
	SBM 368	0112106	17	40	80	90	12	22	M12	Steel	2.3
	SBM 37	0112109	17	60	60	70	12	22	M12	Steel	1.9
	SBM 38	0112110	17	60	60	90	12	22	M12	Steel	2.4
	SBM 40	0112111	17	80	60	90	12	22	M12	Steel	3.3

QUENTES fiberglass jaws

	Clamping range ØD	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Max. tightening torque [Nm]	Screws	m/set [kg]
	90 - 132	TRQ 200-2	0150002	17	40	64	79	19		M12	0.93
		QUENTES 20-3	0150200						8		

Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 170	0112170	17	40	60	420	Steel	7.6
	SBM-ST 171	0112171	17	40	80	420	Steel	10.2
	SBM-ST 172	0112172	17	40	100	420	Steel	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminum	2.8



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for KGH/KGHF 175

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWBL 160	0120151	17	35	40	78	4	15	22	M12	Steel	1.9
	CWB 160	0100005	17	35	40	70		15	22	M12	Steel	1.7
	SWB 160	0120102	17	40	60	70		15	22	M12	Steel	3.1
	SWB-AL 160	0168100	17	40	60	70		15	22	M12	Aluminum	1.2

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NK 120	0147107	17	23	9	19	M12	M12 x 30	70
	NK 121	0145100	17	23	9	22	M12	M12 x 30	70



Technical advice and sales: Tel. +49-7133-103-2750