



SCHUNK chuck jaws for 3 KS 1250

Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	T1 [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-M 800	0121160	30	78	87	190	37	52	32	50	50	M24	Steel	15

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	M [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-M 800	0120452	30	80	110	220	75	45	50	M24	Steel	38.4

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NS 240	0140104	30	41	15	M24	M24 x 50	450



Technical advice and sales: Tel. +49-7133-103-2750