



# SCHUNK Spannbacken für KSH 500



## Backenrohlinge

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | SBM 50      | 0112126    | 25.5      | 60        | 60        | 140       | 20        | 35        | M20       | Stahl     | 4               |
|                                                                                   | SBM 51      | 0112127    | 25.5      | 60        | 80        | 140       | 20        | 35        | M20       | Stahl     | 5               |
|                                                                                   | SBM 52      | 0112128    | 25.5      | 60        | 100       | 140       | 20        | 35        | M20       | Stahl     | 6.5             |
|                                                                                   | SBM 53      | 0112129    | 25.5      | 60        | 100       | 155       | 20        | 35        | M20       | Stahl     | 7.2             |
|                                                                                   | SBM 531     | 0112138    | 25.5      | 60        | 100       | 195       | 20        | 35        | M20       | Stahl     | 9.1             |
|                                                                                   | SBM 5312    | 0112130    | 25.5      | 60        | 120       | 155       | 20        | 35        | M20       | Stahl     | 8.7             |
|                                                                                   | SBM 5315    | 0112131    | 25.5      | 58        | 160       | 155       | 20        | 35        | M20       | Stahl     | 11.5            |
|                                                                                   | SBM 5320    | 0112132    | 25.5      | 58        | 200       | 155       | 20        | 35        | M20       | Stahl     | 14.2            |
|                                                                                   | SBM 57      | 0112134    | 25.5      | 80        | 80        | 155       | 20        | 35        | M20       | Stahl     | 7.2             |
|                                                                                   | SBM 58      | 0112135    | 25.5      | 100       | 100       | 155       | 20        | 35        | M20       | Stahl     | 11.6            |



## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB 400     | 0121107    | 25.5      | 60        | 75        | 140       | 18        | 53        | 31        | 31        | M20       | Stahl     | 8              |

## Segmentbacken

|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SWB-SM 400  | 0169105    | 25.5      | 330       | 150        | 440         | 85        | 55         | 155       | 85        | 35        | M20       | Stahl     | 55.2           |
|  | SWB-SA 400  | 0170105    | 25.5      | 330       | 150        | 440         | 98        | 68         | 160       | 85        | 35        | M20       | Aluminium | 26.2           |

## Verzahnte Stangen



|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Werkstoff | m/Stück<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | SBM-ST 250  | 0112190    | 25.5      | 60        | 100       | 420       | Stahl     | 19.2            |
|                                                                                     | SBM-ST 251  | 0112191    | 25.5      | 58        | 160       | 420       | Stahl     | 30.9            |
|  | SBM-STA 250 | 0112187    | 25.5      | 60        | 100       | 420       | Aluminium | 7               |




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

# SCHUNK Spannbacken für KSH 500

## Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | CWB 400     | 0100008    | 25.5      | 60        | 80        | 140       | 30        | 35        | M20       | Stahl     | 12.6           |
|                                                                                   | SWB 400     | 0120107    | 25.5      | 60        | 90        | 155       | 30        | 35        | M20       | Stahl     | 16             |
|  | SWB-AL 400  | 0168103    | 25.5      | 60        | 100       | 155       | 30        | 35        | M20       | Aluminium | 6.4            |

## Nutenstein

|                                                                                    | Bezeichnung | Ident.-Nr. | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Zyl.-Schraube | Max. zul.<br>Anziehdrehmo-<br>ment<br>[Nm] |
|------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----------|-----|---------------|--------------------------------------------|
|   | NS 200      | 0140103    | 25.5      | 29        | 11         |           | M20 | M20 x 40      | 220                                        |
|  | NK 200      | 0145102    | 25.5      | 29        | 11         | 35        | M20 | M20 x 40      | 220                                        |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750