




SCHUNK Spannbacken für KTHS 200

Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 170	0112170	17	40	60	420	Stahl	7.6
	SBM-ST 171	0112171	17	40	80	420	Stahl	10.2
	SBM-ST 172	0112172	17	40	100	420	Stahl	12.8
	SBM-STA 170	0112173	17	40	60	420	Aluminium	2.8

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-FF 201	0120305	17	40	80	90	18	24	M14	Stahl	5.4

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmoment [Nm]
	FN-T 14	0148112	17	23	9	M14	(D 21 / SW 14)	90



Technische Beratung und Verkauf: Tel. +49-7133-103-2750