




SCHUNK chuck jaws for KTHS 175


Serrated bars

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	Material	m/piece [kg]
	SBM-ST 140	0112165	14	35	60	420	Steel	6.6
	SBM-STA 140	0112166	14	35	60	420	Aluminum	2.4

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	SWB-FF 160	0120302	14	35	40	72	15	21	M12	Steel	1.8

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	FN-T 12	0148111	14	18.5	8	M12	(D 18 / SW 12)	62



Technical advice and sales: Tel. +49-7133-103-2750