



SCHUNK chuck jaws for H0 1 MA 12

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	H-WB 123	0130107	18	50	80	129	40	30	M14	Steel	10.5

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 121	0146103	18	33.5	13.5	30	M14	M14 x 45	130



Technical advice and sales: Tel. +49-7133-103-2750