



SCHUNK Spannbacken für HO 7 MA 10


Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBM 100	0114412	16	40	80	120	13	30	M12	Stahl	3
	JBM 101	0114410	16	40	60	90	13	30	M12	Stahl	1.6
	JBM 102	0114411	16	40	60	110	13	30	M12	Stahl	2.1
	JBM 103	0114413	16	40	100	110	13	30	M12	Stahl	3.4
	JBM 104	0114414	16	50	120	110	13	30	M12	Stahl	5
	JBM 105	0114415	16	60	60	95	13	30	M12	Stahl	2.7
	JBM 106	0114416	16	60	90	95	13	30	M12	Stahl	4
	JBM 107	0114417	16	80	60	95	13	30	M12	Stahl	3.5



Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB-J 102	0131109	16	35	42	83	15	19	25	25	M12	Stahl	1.5

Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	45 - 114	261	SZAJ 20-5	0138120	16	35	53	25	M6	25	M12	Stahl	1.8
	73 - 142	261	SZAJ 20-6	0138125	16	35	53	25	M6	25	M12	Stahl	1.6
	103 - 172	261	SZAJ 20-7	0138122	16	40	53	25	M6	25	M12	Stahl	1.7
	133 - 203	261	SZAJ 20-8	0138127	16	40	53	25	M6	25	M12	Stahl	1.6

Verzahnte Stangen



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 160	0114530	16	40	80	420	Stahl	10.2
	JBM-ST 161	0114531	16	40	120	420	Stahl	15.4
	JBM-ST 162	0114532	16	60	60	420	Stahl	11.4
	JBM-STA 160	0114533	16	40	80	420	Aluminium	3.7




Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für HO 7 MA 10

Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	H-WBL 82	0130602	16	40	40	102	4	20	25	M12	Stahl	3
	H-WB 82	0130120	16	40	60	86		20	25	M12	Stahl	4.1
	H-WB 84	0132146	16	40	40	85		20	25	M12	Stahl	2.6
	H-WBAL 81	0130503	16	40	60	90		20	25	M12	Aluminium	1.5

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 101	0146107	16	26.5	8.5	25	M12	M12 x 35	70



Technische Beratung und Verkauf: Tel. +49-7133-103-2750